



# Prototypes & Short Runs For Prototype Brakes

MOUNTING



## BED RAIL / UNISPACER METHOD

- For prototype or short run straight line punching applications with varying part lengths.
- Quick and easy set up and relocation of holes makes this a preferred mounting method.
- Unispacer fits into bed rail recess.
- Unispacer has two .376" diameter holes on one side to accept unit pilot pins and .376" slot on opposite side for unit front to back adjustment.



**UNIPUNCH**

Exacta Precision Ltd. Toll Free Tel: 1.800.268.5573 Email [Info@exactapunch.com](mailto:Info@exactapunch.com)